# Product Overview **Photoplethysmography (PPG) With Integrated AFE for Optical Biosensing**

Applications like optical heart rate and SpO<sub>2</sub> monitoring are based on the principle of Photoplethysmography (PPG). The primary challenges in PPG signal acquisition on a wrist-worn variable are: (i) small sensor size, (ii) relatively weak signal on wrist (low perfusion index), and (iii) interferers like ambient light and motion artifacts. TI's signal chain for PPG signal acquisition has 3 unique characteristics that help achieve excellent signal quality even in the most challenging conditions: (i) high gain transimpedance amplifier (TIA) to improve the SNR, (ii) DC offset cancellation DAC at the input, and (iii) noise reduction filter to reduce the optical noise bandwidth. These unique features help achieve excellent dynamic range at extremely low power consumption.



### Block Diagram

#### **Recommended Parts**

Device	Description
AFE4432	Ultra-small, ultra-low-power, high-SNR, integrated analog front ends (AFE) for wearable optical biosensing with FIFO
AFE4460	High-SNR, ultra-low-power, integrated AFE for wearable optical biosensing with FIFO
AFE4950	Ultra-small integrated AFE for wearable optical heart-rate monitoring and SpO <sub>2</sub>
AFE4500	Integrated analog front end (AFE) for bioimpedance analysis and electrical and optical biosensing

#### **TI Resources**

- Optical Heart Rate Monitoring (OHRM) on Wearables Application Brief
- Measuring Oxygen Saturation (SpO<sub>2</sub>) on Wearables Application Brief
- DC Estimation for SpO<sub>2</sub> using TI AFEs Application Note (under NDA)

1

Texas Instruments

## IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023, Texas Instruments Incorporated